


SKF SYSTEM 24

Single point automatic lubricator LAGE 125 and LAGE 250

Reliable, reusable lubricator system meets many needs

The LAGE series of the SKF SYSTEM 24 family are single point electro mechanical driven automatic lubricator systems. Suitable for a wide range of applications and operating conditions, the units are reliable and flexible in operation. Supplied ready to use straight from the box and ease of installation makes the units a perfect complement to the comprehensive range of SKF automatic lubricators.

- Electro mechanical driven makes the unit highly reliable in operation
- Available in two sizes: 122 ml (LAGE 125) and 250 ml (LAGE 250) to suit most bearing lubrication applications
- Remote mounting up to 3 meters (10 ft) for grease filled units and 5 meters (16 ft) for oil filled units allows lubrication of bearings in areas with high ambient temperatures, vibration or hazardous environments
- Available filled with various high quality SKF greases and oils, to suit a wide range of bearing applications
- Refill sets consisting of a canister filled with SKF Grease or Oil and a battery pack help ensure reliable lubricator operation
- Flexible user adjustable dispense settings of 1, 3, 6, 9 or 12 months for use in many different applications
- Ingress protection to IP 65 level allows the lubricator to be used in many dusty and wet environments.
- Temperature independent dispense rate, suitable for use in applications with changing temperatures
- Unlike gas powered units, a maximum discharge pressure of 5 bar can be achieved over the whole lubricant dispensing period
- Easy activation using a clearly marked dial helps minimize setting errors
- Transparent lubricant container allows visual inspection of dispense rate, whilst electro mechanical functions are indicated by simple red-green LED indicators.
- UL listed
- Wide range of accessories is available
- SKF SYSTEM 24 LAGE series is fully featured in SKF DialSet 4.0



A B On/off knob and time setting dial

Enable easy activation and dial setting

C LED status indicators

Helps verify operating status

D Drive cover

Easily removable, seals and helps prevent ingress of dirt and moisture

E Electric motor and gearbox

Helps enable constant discharge pressure

F Battery pack

G Piston

Special piston shape helps ensure optimum emptying of lubricator

H Spindle

Rotates to drive piston, enabling lubricant to be dispensed

I Lubricant canister

Filled with high quality SKF lubricant

J Anti-vacuum membrane

Helps prevent vacuum forming



Ordering guide

Lubricant	Description	Product	Complete designation
Greases			
LGWA 2	Multi-purpose EP type grease	Complete unit 125 Complete unit 250 Refill set 125 Refill set 250	LAGE 125/WA2 LAGE 250/WA2 LGWA 2/EML125 LGWA 2/EML250
LGEM 2	High loads, slow rotations	Complete unit 125 Complete unit 250 Refill set 125 Refill set 250	LAGE 125/EM2 LAGE 250/EM2 LGEM 2/EML125 LGEM 2/EML250
LGHB 2	High temperature, loads, plain bearing	Complete unit 125 Complete unit 250 Refill set 125 Refill set 250	LAGE 125/HB2 LAGE 250/HB2 LGHB 2/EML125 LGHB 2/EML250
LGHP 2	High performance polyurea	Complete unit 125 Complete unit 250 Refill set 125 Refill set 250	LAGE 125/HP2 LAGE 250/HP2 LGHP 2/EML125 LGHP 2/EML250
LGFP 2	Food processing industry	Complete unit 125 Complete unit 250 Refill set 125 Refill set 250	LAGE 125/FP2 LAGE 250/FP2 LGFP 2/EML125 LGFP 2/EML250
Oils			
LHMT 68	Medium temperature oil	Complete unit 125 Complete unit 250 Refill set 125 Refill set 250	LAGE 125/HMT68 LAGE 250/HMT68 LHMT 68/EML125 LHMT 68/EML250
LHHT 265	High temperature oil	Complete unit 125 Complete unit 250 Refill set 125 Refill set 250	LAGE 125/HHT26 LAGE 250/HHT26 LHHT 265/EML12 LHHT 265/EML25
LHFP 150	Food compatible, NSF H1 approved oil	Complete unit 125 Complete unit 250 Refill set 125 Refill set 250	LAGE 125/HFP15 LAGE 250/HFP15 LHFP 150/EML12 LHFP 150/EML25



Technical data

Designations		LAGE 125 / LAGE 250
Grease capacity	LAGE 125	122 ml (4,1 fl. oz US)
	LAGE 250	250 ml (8,5 fl. oz US)
Emptying time	User adjustable: 1, 3, 6, 9 and 12 months	
Ambient temperature range	0 °C (-10°C peak) to 50 °C (32 °F (14 °F peak) to 122 °F)	
Maximum operating pressure	5 bar (75 psi)	
Drive mechanism	Electro mechanical	
Connection thread	R 1/4	
Maximum feed line length with:	grease	Up to 3 meters (10 ft) *
	oil	Up to 5 meters (16 ft)
LED status indicators	operating, purging lubricant, empty, malfunction	

UL certification	UL listed T code 59°C - Category BAYZ – 92UM Lubricant dispensing equipment for use in hazardous locations Class I, Division II, Group A, B, C, D Class II, Division II, Group F &G Class III	
	Protection class assembled lubricator	IP 65
	Battery pack	4,5V 2,7 Ah - Alkaline manganese
Recommended storage temperature	20 °C (70 °F)	
Storage life of lubricator	3 years ** (2 years for LGFP 2 and Oils)	
	Total weight	LAGE 125 635 g (22,5 oz) LAGE 250 800 g (28,2 oz)

* The maximum feed line length is dependent on ambient temperature, grease type and back pressure created by the application.

** Storage life is 3 years from production date, which is printed on the side of the canister.
The canister and battery pack may be used even at 12 months setting if activated 3 years from production date.



Ordering details accessories SKF SYSTEM 24

Designation	Description
LAPA 45	Angle connection 45°
LAPA 90	Angle connection 90°
LAPB 3x4E1 *	Brush 30 × 40 mm
LAPB 3x7E1 *	Brush 30 × 60 mm
LAPB 3x10E1 *	Brush 30 × 100 mm
LAPB 5-16E *	Elevator brush, 5 – 16 mm gap
LAPB D2 *	Brush round Ø 20 mm
LAPC 13	Bracket
LAPC 63	Clamp
LAPE 35	Extension 35 mm
LAPE 50	Extension 50 mm
LAPF F1/4	Tube connection female G 1/4
LAPF M1/4	Tube connection male G 1/4
LAPF M1/8	Tube connection male G 1/8
LAPF M3/8	Tube connection male G 3/8
LAPG 1/4	Grease nipple G 1/4
LAPM 2	Y-connection
LAPN 1/8	Nipple G 1/4 – G 3/8
LAPN 1/2	Nipple G 1/4 – G 1/2
LAPN 1/4	Nipple G 1/4 – G 1/4
LAPN 1/4UNF	Nipple G 1/4 – 1/4 UNF

Designation	Description
LAPN 3/8	Nipple G 1/4 – G 3/8
LAPN 6	Nipple G 1/4 – M6
LAPN 8	Nipple G 1/4 – M8
LAPN 8x1	Nipple G 1/4 – M8 × 1
LAPN 10	Nipple G 1/4 – M10
LAPN 10x1	Nipple G 1/4 – M10 × 1
LAPN 12	Nipple G 1/4 – M12
LAPN 12x1.5	Nipple G 1/4 – M12 × 1,5
LAPP 63	Support flange
LAPP 63V	Support flange with non-return valve
LAPT 1000	Flexible tube, 1 000 mm long, 8 × 6 mm
LAPT 5000	Flexible tube, 5 000 mm long, 8 × 6 mm
LAPV 1/4	Non return valve G 1/4
LAPV 1/8	Non return valve G 1/8
LAGE 1-BAT	Battery pack

* Suitable for use with oil filled SKF SYSTEM 24 LAGE 125 and 250 units only